

CUTBACK BITUMEN RC-250 SPECIFICATIONS

Parameters	Min	Max	Test Method
Kinematic viscosity at 60°C mm²/s	250	500	ASTM D2170
Flash point (tag open-cup), °c	27	-	ASTM D3143
Distillate test: distillate, volume percent of total distillate at 360°C:			
To 190°C	-	-	ASTM D402
To 225°C	35	-	ASTM D402
To 260°C	60	-	ASTM D402
To 316°C	80	-	ASTM D402
Residue from distillation to 360°C, percent volume by difference	65	-	ASTM D402
Residue from distillation to 360°C:			
Viscosity at 60°C	60	240	ASTM D5
Penetration at 25°C	80	120	ASTM D5
Ductility at 25°C	100	-	ASTM D113
Solubility in trichloroethylene, %	99	-	ASTM 2042