

CUTBACK BITUMEN RC-30 SPECIFICATIONS

Parameters	Min	Max	Test Method
Kinematic viscosity at 60°C mm²/s	30	60	ASTM D2170
Flash point (tag open-cup), °c	-	-	ASTM D3143
Distillate test: distillate, volume percent of total distillate at 360°C:			
To 190°C	15	-	ASTM D402
To 225°C	55	-	ASTM D402
To 260°C	75	-	ASTM D402
To 316°C	90	-	ASTM D402
Residue from distillation to 360°C:			
Test on residue from distillation Penetration at 25°C, 100g, 5 sec.	80	120	ASTM D5
Ductility at 25°C, cm	100	-	ASTM D402 / ASTM D113
Solubility in trichloroethylene, percent mass	100	-	ASTM 2042
Water, %	-	0.2	ASTM D95