

## CUTBACK BITUMEN SC-3000 SPECIFICATIONS

Parameters	Min	Max	Test Method
<b>Kinematic viscosity at 60°C mm<sup>2</sup>/s</b>	3000	6000	ASTM D2170
<b>Flash point (tag open-cup), °c</b>	107	-	ASTM D3143
<b>Distillate test: distillate, volume percent of total distillate at 360°C:</b>			
<b>Total distillation up to 360°C, volume%</b>	-	5	ASTM D402
<b>Solubility in Trichloroethylene, %</b>	99	-	ASTM D402
<b>Viscosity at 60°C</b>	4000	35000	ASTM D2171
<b>Test on residue from distillation:</b>			
<b>Penetration at 25°C</b>	80	-	ASTM D5
<b>Ductility at 25°C</b>	100	-	ASTM D113